



Fresas Anulares

Descrição	Código
HSS Ø 13 X 25 MM	BA1325
HSS Ø 13 X 50 MM	BA1350
HSS Ø 14 X 25 MM	BA1425
HSS Ø 14 X 50 MM	BA1450
HSS Ø 15 X 25 MM	BA1525
HSS Ø 15 X 50 MM	BA1550
HSS Ø 16 X 25 MM	BA1625
HSS Ø 16 X 50 MM	BA1650
HSS Ø 17 X 25 MM	BA1725
HSS Ø 17 X 50 MM	BA1750
HSS Ø 18 X 25 MM	BA1825
HSS Ø 18 X 50 MM	BA1850
HSS Ø 19 X 25 MM	BA1925
HSS Ø 19 X 50 MM	BA1950
HSS Ø 20 X 25 MM	BA2025
HSS Ø 20 X 50 MM	BA2050
HSS Ø 21 X 25 MM	BA2125
HSS Ø 21 X 50 MM	BA2150
HSS Ø 22 X 25 MM	BA2225
HSS Ø 22 X 50 MM	BA2250
HSS Ø 23 X 25 MM	BA2325
HSS Ø 23 X 50 MM	BA2350
HSS Ø 24 X 25 MM	BA2425
HSS Ø 24 X 50 MM	BA2450
HSS Ø 25 X 25 MM	BA2525
HSS Ø 25 X 50 MM	BA2550
HSS Ø 26 X 25 MM	BA2625
HSS Ø 26 X 50 MM	BA2650
HSS Ø 27 X 25 MM	BA2725
HSS Ø 27 X 50 MM	BA2750
HSS Ø 28 X 25 MM	BA2825
HSS Ø 28 X 50 MM	BA2850
HSS Ø 29 X 25 MM	BA2925
HSS Ø 29 X 50 MM	BA2950
HSS Ø 30 X 25 MM	BA3025
HSS Ø 30 X 50 MM	BA3050
HSS Ø 31 X 25 MM	BA3125
HSS Ø 31 X 50 MM	BA3150
HSS Ø 32 X 25 MM	BA3225
HSS Ø 32 X 50 MM	BA3250
HSS Ø 33 X 25 MM	BA3325
HSS Ø 33 X 50 MM	BA3350
HSS Ø 34 X 25 MM	BA3425
HSS Ø 34 X 50 MM	BA3450

Descrição	Código
HSS Ø 35 X 25 MM	BA3525
HSS Ø 35 X 50 MM	BA3550
HSS Ø 36 X 25 MM	BA3625
HSS Ø 36 X 50 MM	BA3650
HSS Ø 37 X 25 MM	BA3725
HSS Ø 37 X 50 MM	BA3750
HSS Ø 38 X 25 MM	BA3825
HSS Ø 38 X 50 MM	BA3850
HSS Ø 39 X 25 MM	BA3925
HSS Ø 39 X 50 MM	BA3950
HSS Ø 40 X 25 MM	BA4025
HSS Ø 40 X 50 MM	BA4050
HSS Ø 41 X 25 MM	BA4125
HSS Ø 41 X 50 MM	BA4150
HSS Ø 42 X 25 MM	BA4225
HSS Ø 42 X 50 MM	BA4250
HSS Ø 43 X 25 MM	BA4325
HSS Ø 43 X 50 MM	BA4350
HSS Ø 44 X 25 MM	BA4425
HSS Ø 44 X 50 MM	BA4450
HSS Ø 45 X 25 MM	BA4525
HSS Ø 45 X 50 MM	BA4550
HSS Ø 46 X 25 MM	BA4625
HSS Ø 46 X 50 MM	BA4650
HSS Ø 47 X 50 MM	BA4750
HSS Ø 48 X 50 MM	BA4850
HSS Ø 49 X 50 MM	BA4950
HSS Ø 50 X 50 MM	BA5050
HSS Ø 51 X 50 MM	BA5150
HSS Ø 52 X 50 MM	BA5250
HSS Ø 53 X 50 MM	BA5350
HSS Ø 54 X 50 MM	BA5450
HSS Ø 55 X 50 MM	BA5550
HSS Ø 56 X 50 MM	BA5650
HSS Ø 57 X 50 MM	BA5750
HSS Ø 58 X 50 MM	BA5850
HSS Ø 59 X 50 MM	BA5950
HSS Ø 60 X 50 MM	BA6050
ICECUT Ø 1 1/16' X 1'	05B101
ICECUT Ø 1 1/2' X 1'	05B108
ICECUT Ø 1 1/4' X 1'	05B104
ICECUT Ø 1 1/8' X 1'	05B102
ICECUT Ø 1 1/8' X 2'	05B402
ICECUT Ø 1 13/16' X 1'	05B113

Descrição	Código
ICECUT Ø 1 13/16' X 2'	05B413
ICECUT Ø 1 15/16' X 1'	05B115
ICECUT Ø 1 15/16' X 2'	05B415
ICECUT Ø 1 3/16' X 1'	05B103
ICECUT Ø 1 3/16' X 2'	05B403
ICECUT Ø 1 3/4' X 1'	05B112
ICECUT Ø 1 3/4' X 2'	05B412
ICECUT Ø 1 3/8' X 1'	05B106
ICECUT Ø 1 3/8' X 2'	05B406
ICECUT Ø 1 5/16' X 1	05B015
ICECUT Ø 1 5/16' X 1'	05B105
ICECUT Ø 1 5/16' X 2'	05B405
ICECUT Ø 1 5/8' X 2'	05B410
ICECUT Ø 1 5/8' X 1'	05B110
ICECUT Ø 1 7/16' X 1'	05B107
ICECUT Ø 1 7/16' X 2'	05B407
ICECUT Ø 1 7/8' X 1'	05B114
ICECUT Ø 1 7/8' X 2'	05B414
ICECUT Ø 1 9/16' X 1'	05B109
ICECUT Ø 1 9/16' X 2'	05B409
ICECUT Ø 1 X 2'	05B400
ICECUT Ø 1/2' X 2'	05B308
ICECUT Ø 1/2' X 1'	05B008
ICECUT Ø 1' X 1'	05B100
ICECUT Ø 2 1/16' X 2'	05B501
ICECUT Ø 2 1/4' X 2'	05B504
ICECUT Ø 2 1/8' X 1'	05B202
ICECUT Ø 2 1/8' X 2'	05B502
ICECUT Ø 2 1' /16 X 1'	05B201
ICECUT Ø 2 3/16' X 2'	05B503
ICECUT Ø 2 3/8' X 2'	05B506
ICECUT Ø 2 5/16' X 2'	05B505
ICECUT Ø 2' X 1'	05B200
ICECUT Ø 2' X 2'	05B500
ICECUT Ø 3/4 X 1'	05B012
ICECUT Ø 3/4 X 2'	05B312
ICECUT Ø 5/8' X 1'	05B010
ICECUT Ø 7/8' X 1'	05B014
ICECUT Ø 7/8' X 2'	05B314
ICECUT Ø 9/16' X 1'	05B009
ICECUT Ø 9/16' X 2'	05B309
ICECUT Ø 11/16' X 1'	05B011
ICECUT Ø 11/16' X 2'	05B311
ICECUT Ø 1-1/16' X 2'	05B401

Fresas Anulares



Descrição	Código
ICECUT Ø 12 X 30 MM	05E112
ICECUT Ø 12 X 55 MM	05E212
ICECUT Ø 13 X 30 MM	05E113
ICECUT Ø 13 X 55 MM	05E213
ICECUT Ø 13/16" X 1"	05B013
ICECUT Ø 13/16" X 2"	05B313
ICECUT Ø 14 X 30 MM	05E114
ICECUT Ø 14 X 55 MM	05E214
ICECUT Ø 15 X 30 MM	05E115
ICECUT Ø 15 X 55 MM	05E215
ICECUT Ø 15/16" X 2"	05B315
ICECUT Ø 16 X 30 MM	05E116
ICECUT Ø 17 X 30 MM	05E117
ICECUT Ø 18 X 30 MM	05E118
ICECUT Ø 18 X 55 MM	05E218
ICECUT Ø 19 X 55 MM	05E219
ICECUT Ø 20 X 30 MM	05E120
ICECUT Ø 20 X 55 MM	05E220
ICECUT Ø 21 X 30 MM	05E121
ICECUT Ø 21 X 55 MM	05E221
ICECUT Ø 21 X 55 MM	01X721
ICECUT Ø 22 X 30 MM	05E122
ICECUT Ø 23 X 30 MM	05E123
ICECUT Ø 23 X 55 MM	05E223
ICECUT Ø 24 X 30 MM	05E124
ICECUT Ø 24 X 30 MM	01X524
ICECUT Ø 24 X 55 MM	05E224
ICECUT Ø 25 X 30 MM	05E125
ICECUT Ø 25 X 55 MM	05E225
ICECUT Ø 26 X 30 MM	05E126
ICECUT Ø 26 X 55 MM	05E226
ICECUT Ø 27 X 55 MM	05E227
ICECUT Ø 27 X 30 MM	05E127
ICECUT Ø 28 X 30 MM	05E128
ICECUT Ø 29 X 30 MM	05E129
ICECUT Ø 30 X 30 MM	05E130
ICECUT Ø 30 X 55 MM	05E230
ICECUT Ø 31 X 30 MM	05E131
ICECUT Ø 31 X 55 MM	05E231
ICECUT Ø 32 X 30 MM	05E132
ICECUT Ø 32 X 55 MM	05E232
ICECUT Ø 33 X 30 MM	05E133
ICECUT Ø 33 X 55 MM	05E233
ICECUT Ø 34 X 30 MM	05E134

Descrição	Código
ICECUT Ø 34 X 55 MM	05E234
ICECUT Ø 35 X 30 MM	05E135
ICECUT Ø 35 X 55 MM	05E235
ICECUT Ø 36 X 30 MM	05E136
ICECUT Ø 36 X 55 MM	05E236
ICECUT Ø 37 X 30 MM	05E137
ICECUT Ø 37 X 55 MM	05E237
ICECUT Ø 38 X 30 MM	05E138
ICECUT Ø 39 X 30 MM	05E139
ICECUT Ø 39 X 55 MM	05E239
ICECUT Ø 40 X 55 MM	05E240
ICECUT Ø 41 X 30 MM	05E141
ICECUT Ø 42 X 55 MM	05E242
ICECUT Ø 42 X 35 MM	05E142
ICECUT Ø 43 X 30 MM	05E143
ICECUT Ø 43 X 55 MM	05E243
ICECUT Ø 44 X 30 MM	05E144
ICECUT Ø 44 X 55 MM	05E244
ICECUT Ø 45 X 30 MM	05E145
ICECUT Ø 45 X 55 MM	05E245
ICECUT Ø 46 X 30 MM	05E146
ICECUT Ø 46 X 55 MM	05E246
ICECUT Ø 47 X 35 MM	05E147
ICECUT Ø 47 X 55 MM	05E247
ICECUT Ø 48 X 30 MM	05E148
ICECUT Ø 48 X 55 MM	05E248
ICECUT Ø 49 X 30 MM	05E149
ICECUT Ø 49 X 55 MM	05E249
ICECUT Ø 50 X 30 MM	05E150
ICECUT Ø 50 X 55 MM	05E250
ICECUT Ø 51 X 30 MM	05E151
ICECUT Ø 51 X 55 MM	05E251
T.C.T. Ø 61 X 50 MM	TC6150
T.C.T. Ø 62 X 50 MM	TC6250
T.C.T. Ø 63 X 50 MM	TC6350
T.C.T. Ø 64 X 50 MM	TC6450
T.C.T. Ø 65 X 50 MM	TC6550
T.C.T. Ø 66 X 50 MM	TC6650
T.C.T. Ø 67 X 50 MM	TC6750
T.C.T. Ø 68 X 50 MM	TC6850
T.C.T. Ø 69 X 50 MM	TC6950
T.C.T. Ø 70 X 50 MM	TC7050
T.C.T. Ø 71 X 50 MM	TC7150
T.C.T. Ø 72 X 50 MM	TC7250

Descrição	Código
T.C.T. Ø 73 X 50 MM	TC7350
T.C.T. Ø 73 X 75 MM	FM0004
T.C.T. Ø 74 X 50 MM	TC7450
T.C.T. Ø 75 X 50 MM	TC7550
T.C.T. Ø 76 X 50 MM	TC7650
T.C.T. Ø 77 X 50 MM	TC7750
T.C.T. Ø 78 X 50 MM	TC7850
T.C.T. Ø 79 X 50 MM	TC7950
T.C.T. Ø 80 X 50 MM	TC8050
T.C.T. Ø 81 X 50 MM	TC8150
T.C.T. Ø 82 X 50 MM	TC8250
T.C.T. Ø 83 X 50 MM	TC8350
T.C.T. Ø 84 X 50 MM	TC8450
T.C.T. Ø 85 X 50 MM	TC8550
T.C.T. Ø 86 X 50 MM	TC8650
T.C.T. Ø 87 X 50 MM	TC8750
T.C.T. Ø 88 X 50 MM	TC8850
T.C.T. Ø 89 X 50 MM	TC8950
T.C.T. Ø 90 X 50 MM	TC9050
T.C.T. Ø 91 X 50 MM	TC9150
T.C.T. Ø 92 X 50 MM	TC9250
T.C.T. Ø 93 X 50 MM	TC9350
T.C.T. Ø 94 X 50 MM	TC9450
T.C.T. Ø 95 X 50 MM	TC9550
T.C.T. Ø 96 X 50 MM	TC9650
T.C.T. Ø 97 X 50 MM	TC9750
T.C.T. Ø 98 X 50 MM	TC9850
T.C.T. Ø 99 X 50 MM	TC9950
T.C.T. Ø 100 X 50 MM	TC10050
T.C.T. Ø 100 X 75 MM	FM0009
T.C.T. Ø 130 X 75 MM	FM0008